FD3-MK144J00V00E0B



IFDH 3000 Indoor Fiber Distribution Hub, 144F, loose tube pigtails

Product Classification

Regional Availability

North America

Product Type Fiber distribution hub

Product Series IFDH 3000

General Specifications

Access Front
Adapters, quantity 144

 Cable Type
 Pigtails - Stranded

Color Putty white

Distribution Cables, quantity 12
Fibers per Distribution Cable, quantity 12
Fibers per Feeder Cable, quantity 24

Front Door Type Single hinged

InterfaceSC/APCMountingWallPort, quantity144Splitter Slots, quantity18

Dimensions

 Height
 736.6 mm | 29 in

 Width
 533.4 mm | 21 in

 Depth
 368.3 mm | 14.5 in

Material Specifications

Finish Powder coated

Material Type Steel

COMMSCOPE®

FD3-MK144J00V00E0B

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

