

FD3-AG432J00GCBP7



FDH 3000 Fiber Distribution Medium Cabinet, 432F distribution loaded, SC/APC, no splitters, single armor loose tube, 100 ft, 2x216F distribution cable assembly, 72F feeder

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Armored - Single Loose Tube
Color	Putty white
Distribution Cables, quantity	2
Distribution Ports, quantity	432
Fibers per Distribution Cable, quantity	216
Fibers per Feeder Cable, quantity	72
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	24

Dimensions

Height	1,066.8 mm 42 in
Width	685.8 mm 27 in
Depth	457.2 mm 18 in
Cable Length	30.48 m 100 ft
Enclosure Size	Medium

Material Specifications

Finish	Powder coated
Material Type	Aluminum

FD3-AG432J00GCBP7

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet