

C400F-NMSM

CNT-400-FR CNT® Jumper N-MALE, SMA-MALE Fire retardant 50-ohm JUMPER Fire Retardancy Test Method IEC 60332.



Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-400

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-400
Interface, Connector A	SMA Male
Interface, Connector B	N Male
Specification Sheet Revision Level	A

Dimensions

Nominal Size	0.400 in
---------------------	----------

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	14.99

Jumper Assembly Sample Label

C400F-NMSM



Included Products

- 400APNM-C – Type N Male for CNT-400 braided cable
- CNT-400-FR – CNT-400-FR, CNT[®] 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, Dca s2 d2 Compliant