



Indoor/Outdoor Low Smoke Zero Halogen, TeraSPEED® Central Loose Tube Fiber Optic Cable, 4-fiber, Singlemode OS2, Gel-filled, black. Provides Rodent Resistance.

- non-metallic construction reinforced by E-glass yarns, which provide rodent resistance and higher tensile strength

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-CN

## General Specifications

<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE 760254735 INT/EXT RODENT RESIST GLT 4X9/125 OS2 (Serial NUMBER) (METRE MARK)
<b>Fibers per Subunit, quantity</b>	4
<b>Total Fiber Count</b>	4

## Dimensions

<b>Cable Length</b>	2000 m   6,561.68 ft
<b>Diameter Over Jacket</b>	6.4 mm   0.252 in

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	129.5 mm   5.098 in
<b>Minimum Bend Radius, unloaded</b>	80 mm   3.15 in
<b>Tensile Load, long term, maximum</b>	650 N   146.126 lbf
<b>Tensile Load, short term, maximum</b>	1250 N   281.011 lbf

# 810010219/DB | C-004-CN-8W-M04BK/28G/GY/E

---

## Optical Specifications

**Fiber Type** OS2

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.25 dB/km @ 1,300 nm | 0.35 dB/km @ 1,550 nm | 0.45 dB/km @ 1,310 nm

**Standards Compliance** TIA-492CAAB (OS2)

## Environmental Specifications

**Operating Temperature** -20 °C to +70 °C (-4 °F to +158 °F)

**EN50575 CPR Cable EuroClass Fire Performance** Eca

**Environmental Space** Low Smoke Zero Halogen (LSZH)

## Packaging and Weights

**Cable weight** 48 kg/km | 32.255 lb/kft

## Included Products

CS-8W-250-EMEA – LightScope ZWP® Singlemode Fiber  
250um

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable