# MCG22HDX15-12-H10



G22HDX Monopole Sector Frame with extended face, 15 ft x 2.88 in OD face pipes. Includes twelve  $2.88 \text{ OD} \times 120$  in antenna pipes

#### **Product Classification**

Product Type High capacity monopole sector frame

Product Brand PIM-guard

Product Series G2

# General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 12
Sectors, quantity 3

#### Dimensions

**Face Width** 4.572 m | 15 ft

**Width** 4,572 mm | 180 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

Mounting Diameter, maximum 1270 mm | 50 in

**Mounting Diameter, minimum** 381 mm | 15 in

 Pipe Outer Diameter
 73.025 mm | 2.875 in

 Stand-off Distance
 1,066.8 mm | 42 in

### Material Specifications

Material Type Hot dip galvanized steel

# Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222

### Packaging and Weights

Included Mounting hardware | Plain end pipes (12) | Ring mounts (2) | Sector frames (3) | Stiff arm

Page 1 of 2



# MCG22HDX15-12-H10

Packaging quantity

**Weight, net** 1,127.88 kg | 2,486.55 lb

1

# Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



### \* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

