


# MC-KD8M-B



Heavy Duty Double T-Arm Monopole Mount Base Kit, Includes (2) Ring Mounts for 15"-50" OD Monopole, 8 ft x 3-1/2" OD face pipes. Antenna Pipes not included.

Heavy Duty Double T-Arm mount design for Monopole applications featuring sturdy corner tie-backs for added stability. Includes 3-1/2" OD face pipes. Antenna Pipes not included.

## Product Classification

**Product Type** Monopole T-frame kit

## General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

**Pipe, quantity** 0

**Sectors, quantity** 3

## Dimensions

**Face Width** 2,438 mm | 8 ft

**Width** 2,438.4 mm | 96 in

**Mounting Diameter, maximum** 1270 mm | 50 in

**Mounting Diameter, minimum** 381 mm | 15 in

**Stand-off Distance** 1,244.6 mm | 49 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact your local ANDREW representative

**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Ring mounts (2) | Stand-off arms

**Packaging quantity** 1

**Weight, net** 632.444 kg | 1,394.3 lb

# MC-KD8M-B

---

\* Footnotes

**Wind Rating**

BWS—Base Wind Speed; FBC—Florida Building Code

