



Fiber Optic Pigtail, 12 color kit, OM4, SC to Stub, 0.9 mm diameter, 1.5 m

Product Classification

Regional Availability	EMEA
Product Type	Fiber pigtail, jacketed
Product Series	OCP

General Specifications

Connector A, quantity	12
Color, boot A	Aqua
Color, connector A	Beige
Interface, Connector A	SC/UPC
Total Fibers, quantity	12

Dimensions

Cord Length	1.5 m 4.921 ft
Diameter Over Jacket	0.9 mm 0.035 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
----------------------------	-------------------------------

Packaging and Weights

Packaging quantity	12
---------------------------	----

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

EH0194-007 | OCP-S5-15DGEN-XX-(12)-AP

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

