

# 760258356 | PPL-FA-4U-HCM

---



Propel 4RU front access fiber panel for Propel XFrame. Accepts 24, 16 fiber or 48, 8 fiber Propel ULL modules, splice cassettes or 8 port/4 port adapter packs

- Panel comes with 24 carriers to allow for all front access using standard Propel components. Incoming cable and patch cords are routed at the front of the panel
- HCM (Horizontal Cable Management) panels: HCM panels maximize density within the frame. Patch cords are routed across the front of the panel providing maximum frame density
- For use with 8 fiber or 16 fiber Propel components

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Color</b>	Gray
<b>Interface, front</b>	Unloaded
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	4
<b>Shelf Movement</b>	Fixed

## Dimensions

<b>Height</b>	178 mm   7.008 in
<b>Width</b>	483 mm   19.016 in

## Material Specifications

<b>Material Type</b>	Aluminum   Steel
----------------------	------------------

## Environmental Specifications

<b>Safety Standard</b>	UL
------------------------	----

760258356 | PPL-FA-4U-HCM

---

## Packaging and Weights

**Packaging quantity**      1