760250370



Fiber Optic Patch Cord, OS2, LC/UPC-LC/UPC, 2-fiber RBR, 2.0 mm subunits, 16 m, yellow, 39" breakouts

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

 Regional Availability
 Latin America | North America

 Product Type
 Fiber distribution cable assembly

Product Series FPM

Government RequirementsBuild America Buy America (BABA) compliant*

Blue

Yellow

General Specifications

Connector A, quantity2Color, boot ABlueColor, connector ABlue

Connector B, quantity2Color, boot BBlue

Construction Type Stranded
Interface, Connector A LC/UPC

Interface, Connector B LC/UPC

Location of ManufacturingClaremont, North Carolina

Total Fibers, quantity 2

Dimensions

Jacket Color

Color, connector B

Breakout Length, connector A990.6 mm | 39 inBreakout Length, connector B990.6 mm | 39 inCord Length16 m | 52.493 ft



760250370

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2

Insertion Loss, maximum, connector A 0.3 dB

Insertion Loss, maximum, connector B 0.3 dB

Return Loss, minimum, connector A 55 dB

Return Loss, minimum, connector B 55 dB

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

760004416 – Fiber indoor cable, TeraSPEED® Riser Distribution, Singlemode G.652.D and G.657.A1, 4 fiber R-004-DS-8W-FSUYL single-unit, Feet jacket marking, Yellow jacket color

Page 2 of 2