



IFEB Fibre Optic Wrap around Feeder Cable Sealing Kit for 1 cable with a cable diameter of max 20 mm

- Feeder cable seal for IFEB-20
- For cable diameter of 10mm to 20mm
- Indoor use only
- IEC-60529 IP50
- Cable retention max 25N per cable
- Includes cable termination baseplate and strength member fixation (1)
- For additional cables IFEB-SEAL-F-ADD is required (ordered separately)

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Cable sealing
Product Series	IFEB-20

General Specifications

Cable Ports, quantity	1
------------------------------	---

Environmental Specifications

Installation temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Indoor
Flammability Rating	UL 94 V-0
Qualification Standards	IEC 60529, IP50 IEC 61753-1 Ed.2 2018 - Category C

Packaging and Weights

Included	Cable attachment baseplate (1) Cable attachment strength member (1) Cable seal 1x20 assembly (1) Protection Tape (1) Screw (2) Tie wrap (2)
Packaging quantity	1
Packaging Type	Box

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

760260219 | IFEB-SEAL-F-1x20

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

