



REGAL RLS 1.2 GHz RF splitter, 3 unbalanced outputs, AC power#passing

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

- Support DOCSIS® 3.1 expanded bandwidth up to 1218 MHz
- Maintain existing Regal installed base with compatible faceplate upgrades
- Easily configured to enable or block AC power as needed in the network
- Faceplate only options for cost-effective upgrades to existing Regal deployments
- Support aerial or pedestal installation with flexible design
- Protect valuable network equipment investment with heavy surge suppression options available

Product Classification

| | |
|-----------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Product Type | Splitter |
| Product Series | REGAL |
| Government Funding | Build America Buy America (BABA) compliant* |

General Specifications

| | |
|---------------------------|---|
| Location of Manufacturing | Waived per BABA waiver for BEAD Program |
|---------------------------|---|

Dimensions

| | |
|--------|--------------------|
| Height | 116.84 mm 4.6 in |
| Depth | 76.2 mm 3 in |
| Length | 139.7 mm 5.5 in |

Electrical Specifications

| | |
|----------------------------|--------------|
| Current Handling, ac ports | 20 A |
| Current Handling, RF ports | 15 A |
| Operating Frequency Band | 5 – 1218 MHz |
| Surge Protection | No |

Environmental Specifications

1509891-015 | RLS12-3R-15A

Operating Temperature -40 °C to +60 °C (-40 °F to +140 °F)

Packaging and Weights

Weight 0.68 kg | 1.5 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

