

OM6HHSYHN-1XR2XC112M



Opti Max™ 1.2 GHz Deep OM6000 Optical Node configured with Remote PHY Device (RPD)

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Optical node platform
Product Series	OM6000
Government Requirements	Build America Buy America (BABA) compliant*

General Specifications

Location of Manufacturing	Waived per BABA waiver for BEAD Program
----------------------------------	-----------------------------------------

Electrical Specifications

Input Voltage Range, ac	44–90 V
--------------------------------	---------

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Relative Humidity	5%–95%, non-condensing

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

