


## ConQuest® Cable in Conduit, 1 1/4 in, SCH 40, orange (P3® 625 JCASS)



- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or are the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

### OBSOLETE

This product was discontinued on: **March 13, 2015**

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Coaxial cable-in-conduit
<b>Product Brand</b>	ConQuest®
<b>Product Series</b>	625 Series

## General Specifications

<b>Cable Type</b>	625 Series
<b>Cable-In-Conduit Type</b>	P3® in duct
<b>Color</b>	Orange
<b>Conduit Type</b>	Non-toneable
<b>Wall Type</b>	Smooth

## Dimensions

<b>Length</b>	731.52 m   2400 ft
<b>Wall Thickness Designation</b>	SCH 40
<b>Nominal Size</b>	1-1/4 in

## Packaging and Weights

<b>Weight, net</b>	653.304 kg/km   439 lb/kft
--------------------	----------------------------

# CX3350054 | 1250040P3625JCASS COEX

---

## Included Products

- 530101403 P3® 625 JCASS SM MT – 75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground
- 5308103 P3® 625 JCASS – 75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground