


CX3750009 | 200T040P3625JCASS COEX

ConQuest® Cable in Conduit, 2 in, SCH 40, terracotta (P3® 625 JCASS)



Product Classification

Product Type	Coaxial cable-in-conduit
Product Brand	ConQuest®
Product Series	625 Series

General Specifications

Cable Type	625 series
Cable-In-Conduit Type	P3® in duct
Color	Terracotta
Conduit Type	Non-toneable
Wall Type	Smooth

Dimensions

Length	731.52 m 2400 ft
Wall Thickness Designation	SCH 40
Nominal Size	2 in

Packaging and Weights

Weight, net	918.197 kg/km 617 lb/kft
-------------	----------------------------

Included Products

530101403 P3® 625 JCASS SM MT	-	75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground
5308103 P3® 625 JCASS	-	75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground
CX3799999 200T040 EMPTY DUCT COEX	-	ConQuest® Empty Conduit, 2 in, SCH 40, terracotta

