


## ConQuest® Cable in Conduit, 2 in, SDR 13.5, terracotta (P3® 875 JCASS)



- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or are the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

### OBSOLETE

This product was discontinued on: **March 13, 2015**

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Coaxial cable-in-conduit
<b>Product Brand</b>	ConQuest®
<b>Product Series</b>	875 Series

## General Specifications

<b>Cable Type</b>	875 Series
<b>Cable-In-Conduit Type</b>	P3® in duct
<b>Color</b>	Terracotta
<b>Conduit Type</b>	Non-toneable
<b>Wall Type</b>	Smooth

## Dimensions

<b>Length</b>	731.52 m   2400 ft
<b>Wall Thickness Designation</b>	SDR 13.5
<b>Nominal Size</b>	2 in

## Packaging and Weights

<b>Weight, net</b>	1,172.673 kg/km   788 lb/kft
--------------------	------------------------------

# CX3750075 | 200T135P3875JCASS COEX

---

## Included Products

- 530101403 P3® 625 JCASS SM MT - 75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground
- CX3799839 200T135 EMPTY DUCT COEX - ConQuest® Empty Conduit, 2 in, SDR 13.5, terracotta