# CK6451-000 | FOSC-OPGW-B4NT-O-NNN



FOSC® OPGW B Fiber Optic Splice Closure, Heat Shrink Cable sealing, butt type, no pre-installed trays

#### Product Classification

Regional Availability	Asia   EMEA   Latin America   North America
Product Type	Single-ended, round fiber closure
Product Brand	FOSC®
Product Series	FOSC OPGW
General Specifications	
Cable Entry Drop Port Style	Round
Cable Entry Main Port Style	Round
Cable Ports Quantity, total	1 oval port (2 cables) + 4 round ports
Cable Sealing Type	Heat shrink
Closure Sealing Type	Dome-to-base clamp with O-ring
Closure Style	Single-ended
Color	Black
Ground Feed-through	None
Mounting	Pole   Strand   Wall
Network Area Type	Feeder
Splice Tray Included, quantity	0
Splice Tray Type Included	No trays
Splicing Capacity, Mass Fusion, maximum	144
Splicing Capacity, Single Fusion, maximum	96
Splicing Capacity, Single Splice, 12 fibers, maximum	96
Splicing Capacity, Single Splice, 6 fibers, maximum	48
Splicing Type, Supported	Mass fusion   Single fusion
Dimensions	

Dimensions

Height

240 mm | 9.449 in


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



# CK6451-000 | FOSC-OPGW-B4NT-O-NNN

Width	202 mm   7.953 in
Length	715 mm   28.15 in
Main Cable Diameter, maximum	19 mm   0.748 in

### Ordering Tree



Same options are for 2nd cable feed-through, except option E

### Material Specifications

Material Type

Impact-resistant polymer

#### **Environmental Specifications**

Environmental Space	Above ground
Qualification Standards	IEC 61300, 6 m waterhead
Packaging and Weights	
Packaging quantity	1
Packaging Type	Box   Carton
Weight, net	18 kg   39.683 lb

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024



## CK6451-000 | FOSC-OPGW-B4NT-O-NNN

ROHS

UK-ROHS

Compliant Compliant



Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 22, 2024

