

# CSC3-U5A1A1BA000



NOVUX™ CSC100 Compact Fiber Closure, splice only, no adapters, no splitters, no mounting, black

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

This product will be discontinued on: **August 4, 2023**

Replaced By:

CSC3-M5A1A1BA000 NOVUX™ CSC100 Compact Fiber Closure, splice only, no adapters, no splitters, no mounting, black

## Product Classification

<b>Regional Availability</b>	Asia   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	NOVUX™
<b>Product Series</b>	CSC 100

## General Specifications

<b>Cable Ports Quantity, total</b>	3 round ports + 6 multi-out ports (12 cables)
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Hinged with latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Pole   Wall
<b>Port Type</b>	No adapter
<b>Port, quantity</b>	0
<b>Splitter Type</b>	No splitter

# CSC3-U5A1A1BA000

---

**Splitter, quantity** 0

## Dimensions


**Height** 284 mm | 11.181 in

**Width** 117 mm | 4.606 in

**Depth** 77 mm | 3.031 in

# CSC3-U5A1A1BA000

## Dimension Drawing




## Port Configuration

Position	Cable diameter	
	mm	Inches
Feeder cable	≤ 14	≤ 0.55
Branch cable	≤ 12	≤ 0.47
Single drops	≤ 8 (flat cable: 8 x 4,5)	≤ 0.32 (flat cable: 0.32 x 0.18)
Dual drops	≤ 6,2	≤ 0.25

## Ordering Tree

# CSC3-U5A1A1BA000



## Environmental Specifications

<b>Environmental Space</b>	Outdoor
<b>UV Resistance</b>	UV stabilized

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
TL 9000:2016 (R6)	Compliant to this quality management practice
UK-ROHS	Compliant



CSC3-U5A1A1BA000

---