


# CX5455-000 | FIST-GPSTF-12-AAN-2

---



FIST GPST Fiber Patch Tray, 12/24 ports, no adapters, 15 in, gray, left /right patch cord routing

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Fiber patch tray
<b>Product Brand</b>	FIST®
<b>Product Series</b>	FIST-GPST

## General Specifications

<b>Functionality</b>	Patching
<b>Color</b>	Gray
<b>Interface, front</b>	Unloaded
<b>Patch Cord Entry Location</b>	Front, left side   Front, right side
<b>Patching Capacity, maximum</b>	12
<b>Splicing Capacity, maximum</b>	0
<b>Total Ports, quantity</b>	12

## Dimensions

<b>Height</b>	16 mm   0.63 in
<b>Width</b>	315 mm   12.402 in
<b>Depth</b>	190 mm   7.48 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

<b>Operating Temperature</b>	-5 °C to +45 °C (+23 °F to +113 °F)
------------------------------	-------------------------------------

# CX5455-000 | FIST-GPSTF-12-AAN-2

---

**Storage Temperature** -30 °C to +60 °C (-22 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

