

FMT-GM7M71000-S72P



FMT Fiber Termination Panel, with sliding tray and IFC cable, 72 SC/UPC, singlemode, 2RU, 19 in, putty white, Stub tail at far end

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with IFC cable
Product Series	FMT

General Specifications

Functionality	Patching
Body Style	Symmetrical
Color	Black + Putty white (front)
Interface, front	SC/UPC
Rack Type	EIA 19 in EIA 23 in
Rack Units	2
Shelf Movement	Sliding
Total Ports, quantity	72

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	279.91 mm 11.02 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

FMT-GM7M71000-S72P

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

