

# LSX-L75243-A-SPL

---



LSX Fiber Termination/Splice Panel 8 Ru, 288 - SC/UPC, Singlemode Ribbon

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	LGX

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Application</b>	Used in LSX-style frames only
<b>Cable Stub Type</b>	Pigtails, ribbon
<b>Color</b>	Putty white
<b>Color, front</b>	White
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	SC/UPC
<b>Rack Type</b>	EIA 23 in
<b>Rack Units</b>	8
<b>Shelf Movement</b>	Fixed
<b>Splicing Type</b>	Mechanical, mass fusion
<b>Total Ports, quantity</b>	288

## Dimensions

<b>Height</b>	279.4 mm   11 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	381 mm   15 in

# LSX-L75243-A-SPL

---

## Material Specifications

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

