

LSX-TK1122-A-SPL



LSX Fiber Termination/Splice Panel 6 Ru, 144 - LC/UPC, Singlemode Stranded

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	LGX

General Specifications

Functionality	Patching Splicing
Application	Used in LSX-style frames only
Cable Stub Type	Pigtails, stranded
Color	Putty white
Color, front	White
Growth Configuration	Fully loaded
Interface, front	LC/UPC
Rack Type	EIA 19 in EIA 23 in
Rack Units	6
Shelf Movement	Fixed
Splicing Type	Heat shrink, single fiber fusion
Total Ports, quantity	144

Dimensions

Height	228.6 mm 9 in
Width	482.6 mm 19 in
Depth	304.8 mm 12 in

Material Specifications

Finish	Powder coated
---------------	---------------

LSX-TK1122-A-SPL

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS1

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

