


# RDT-SJ24J00D4502A

---



RapidFiber® FDT Distribution Terminal, 24-fiber, SC/APC, MPO at far end, 450 ft

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution terminal
<b>Product Brand</b>	RapidFiber®
<b>Product Series</b>	FDT

## General Specifications

<b>Adapters, quantity</b>	24
<b>Cable Type</b>	Pigtails - Stranded
<b>Color</b>	Putty white
<b>Interface</b>	SC/APC
<b>Interface, stub</b>	MPO
<b>Mounting</b>	Wall
<b>Port, quantity</b>	24

## Dimensions

<b>Height</b>	152.4 mm   6 in
<b>Width</b>	228.6 mm   9 in
<b>Depth</b>	101.6 mm   4 in
<b>Cable Length</b>	137.16 m   450 ft

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Optical Specifications

# RDT-SJ24J00D4502A

---

**Fiber Mode** Singlemode

## Environmental Specifications

**Environmental Space** Indoor

**Qualification Standards** NEMA, Type 12

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

