RDT-SM12N00D18490



RapidFiber® Mini-RDT Distribution Terminal, 12-fiber, SC/UPC, Indoor /outdoor cable, 603 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

Product Classification

Regional Availability North America

Product Type Fiber distribution terminal

Product Brand RapidFiber®

Product Series Mini-RDT

General Specifications

Adapters, quantity 12

Cable Entry LocationBottom leftBottom rightCable TypeIndoor/outdoor - Stranded

Color Gray
Interface SC/UPC

Interface, stub No connector

Mounting Wall
Port, quantity 12

Dimensions

 Height
 200 mm | 7.874 in

 Width
 140 mm | 5.512 in

 Depth
 60 mm | 2.362 in


Cable Length 183.79 m | 602.986 ft

Outer Cable Diameter 4 mm | 0.157 in


Dimension Drawing



RDT-SM12N00D18490



Ordering Tree



RDT-SM12N00D18490

Material Specifications

Material Type Plastic

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

