


# 2-2122149-3 | FMS-K-2-B-E-L5F-12-IN99-0-SP



FMS Fiber Optic Termination/Splice Panel, 1U, 19 in, 24 LC/UPC, multimode, OM3, black

## Product Classification

<b>Regional Availability</b>	India
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	FMS

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Body Style</b>	Symmetrical
<b>Cable Exit Location</b>	Rear, left side   Rear, right side
<b>Color</b>	Black
<b>Growth Configuration</b>	Partially loaded
<b>Interface, front</b>	LC/UPC
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding
<b>Splice Trays Included, quantity</b>	2
<b>Splicing Type</b>	Heat shrink, single fiber fusion
<b>Total Ports, quantity</b>	24

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	320 mm   12.598 in

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	OM3
<b>Insertion Loss, maximum</b>	0.3 dB
<b>Return Loss, minimum</b>	20 dB

## Packaging and Weights

<b>Included</b>	Mounting hardware
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

