## 300001746146 | FD3-AE216J00JCBP1P



FDH 3000 Small Fiber Distribution Pole Mount Cabinet, 216F, SC/APC, no splitters, dielectric loose tube, 100 ft, 12F

### **Product Classification**

**Regional Availability** North America

Fiber distribution hub **Product Type** 

FDH 3000 **Product Series** 

General Specifications

Access Front

Dielectric - Loose Tube **Cable Type** 

Color Putty white

1 **Distribution Cables, quantity** 

288 **Distribution Ports, quantity** 

Fibers per Distribution Cable, quantity 216

12 Fibers per Feeder Cable, quantity

Interface, Input SC

Interface Feature, Input APC

Pole Mounting

Splitter Slots, quantity 12

### Dimensions

Height 762 mm | 30 in

Width 686 mm | 27.008 in Depth 457 mm | 17.992 in **Cable Length** 30.48 m | 100 ft

**Enclosure Size** Small

Material Specifications

**Finish** Powder coated

**Material Type** Aluminum

Page 1 of 2

# 300001746146 | FD3-AE216J00JCBP1P

### **Environmental Specifications**

Environmental Space Aerial

Packaging and Weights

Packaging quantity

Packaging Type Pallet

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

