300001761664 | FD3-AC096J00JJBP1P



FDH 3000 Fiber Distribution Extra Small Pole Mount Cabinet, 96F, SC /APC, no splitters, die. loose tube, 100 ft, 12F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeDielectric - Loose Tube

Color Putty white

Distribution Cables, quantity 2

Distribution Ports, quantity 144

Fibers per Distribution Cable, quantity 48

Fibers per Feeder Cable, quantity 12

Interface, Input SC

Interface Feature, Input APC

Mounting Pole

Splitter Slots, quantity 9

Dimensions

Height 762 mm | 30 in

 Width
 533 mm | 20.984 in

 Depth
 356 mm | 14.016 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Extra small

Material Specifications

Finish Powder coated

Material Type Aluminum

COMMSC PE°

300001761664 | FD3-AC096J00JJBP1P

Environmental Specifications

Environmental Space Aerial

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

