## 300001765589 | FD3-AC072J00JABP1P



FDH 3000 Fiber Distribution Extra Small Cabinet, 72F, SC/APC, no splitters, dielectric loose tube, 100 ft, 12F

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution hub

Product Series FDH 3000

General Specifications

**Access** Front

Cable Type Dielectric - Loose Tube

**Color** Putty white

Distribution Cables, quantity

**Distribution Ports, quantity** 144

Fibers per Distribution Cable, quantity 72

Fibers per Feeder Cable, quantity 12

Interface, Input SC

Interface Feature, Input APC

**Mounting** Pole

Splitter Slots, quantity 9

Dimensions

**Height** 762 mm | 30 in

 Width
 533 mm | 20.984 in

 Depth
 356 mm | 14.016 in

 Cable Length
 30.48 m | 100 ft

**Enclosure Size** Extra small

Material Specifications

**Finish** Powder coated

Material Type Aluminum

COMMSC PE°

# 300001765589 | FD3-AC072J00JABP1P

### **Environmental Specifications**

Environmental Space Aerial

Packaging and Weights

Packaging quantity

Packaging Type Pallet

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

