## 393964-000 | FIST-GPS2-I-NNN-0



FIST-GPS2 Fiber Panel for holding up to 6 GPST Patch/Splice Trays, unloaded, 3RU, 19 in, gray

### Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Brand	FIST®
Product Series	FIST-GPS2

#### General Specifications

Functionality	Patching   Splicing	
Application	Used in FIST-GR3-style frames only	
Color	Gray	
Color, front	Gray	
Growth Configuration	Unloaded	
Interface, front	Unloaded	
Rack Type	EIA 19 in   ETSI 600 mm	
Rack Units	3	
Shelf Movement	Sliding	

#### Dimensions

Height	133.35 mm   5.25 in
Width	482.6 mm   19 in

#### Material Specifications

Finish	Powder coated
Material Type	Galvanized steel

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2023



# 393964-000 | FIST-GPS2-I-NNN-0

## **Environmental Specifications**

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Relative Humidity	Up to 93%, non-condensing

#### Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 4, 2023

