

F3X-E288JJBBB0000



FDH 3000 Small Fiber Distribution Cross-Connect/Distribution Hub, 144F, SC APC, dielectric loose tube, 100 ft

Product Classification

Regional Availability	North America
Product Type	Fiber cross-connect hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	2
Distribution Ports, quantity	288
Fibers per Distribution Cable, quantity	144
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	12

Dimensions

Height	762 mm 30 in
Width	685.8 mm 27 in
Depth	457.2 mm 18 in
Cable Length	30.48 m 100 ft
Enclosure Size	Small

Material Specifications

Finish	Powder coated
Material Type	Steel

F3X-E288JJBBB0000

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

