FD3-AB072J00AABP1



Enhanced Mini FDH, 72F loaded pole/wall mounted cabinet, SC/APC, PNP splitter capable, I/O Dielectric Ribbon Cable, 100ft stubs using a 1x72F distribution cable assembly and a 1x12F feeder

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeDielectric - Ribbon

Color Putty white

Distribution Cables, quantity 1

Distribution Ports, quantity 72

Fibers per Distribution Cable, quantity 72

Fibers per Feeder Cable, quantity 12

Interface, Input SC

Interface Feature, Input APC

Mounting Pole | Wall

Splitter Slots, quantity 8

Dimensions

 Height
 584.2 mm | 23 in

 Width
 330.2 mm | 13 in

 Depth
 203.2 mm | 8 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Mini

Material Specifications

Finish Powder coated

Material Type Aluminum

Page 1 of 2



FD3-AB072J00AABP1

Environmental Specifications

Environmental Space Above ground | Aerial

Qualification Standards Telcordia GR-3123-CORE | Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

