

# FL1-6PCSC003

---

FL1000 Fiber Optic Adapter Pack, singlemode, SC/UPC, 3 duplex adapters, with pigtails

## Product Classification

|                              |                                  |
|------------------------------|----------------------------------|
| <b>Regional Availability</b> | Latin America   North America    |
| <b>Product Type</b>          | Fiber adapter pack with pigtails |
| <b>Product Series</b>        | FL1000                           |

## General Specifications

|                               |                     |
|-------------------------------|---------------------|
| <b>Adapter Color</b>          | Blue                |
| <b>Adapters, quantity</b>     | 6                   |
| <b>Cable Type</b>             | Pigtails - Stranded |
| <b>Color</b>                  | Putty white         |
| <b>Interface</b>              | SC                  |
| <b>Interface Feature</b>      | Standard            |
| <b>Total Fibers, quantity</b> | 6                   |

## Dimensions

|                       |                    |
|-----------------------|--------------------|
| <b>Height</b>         | 27.94 mm   1.1 in  |
| <b>Width</b>          | 149.86 mm   5.9 in |
| <b>Pigtail Length</b> | 3 m   9.843 ft     |

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
|-------------------|------------|

## Environmental Specifications

|                            |        |
|----------------------------|--------|
| <b>Environmental Space</b> | Indoor |
|----------------------------|--------|

## Packaging and Weights

|                           |     |
|---------------------------|-----|
| <b>Packaging quantity</b> | 1   |
| <b>Packaging Type</b>     | Bag |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b> |
|---------------|-----------------------|
|---------------|-----------------------|

# FL1-6PCSC003

---

|            |  |
|------------|--|
| CHINA-ROHS | Above maximum concentration value  |
| REACH-SVHC | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS       | Compliant/Exempted   |
| UK-ROHS    | Compliant/Exempted   |

