

760188433 | 360G2-iP-2U-288F-LC-DM-OS-UHD



SYSTIMAX 360™ iPatch® InstaPATCH 2U 288F-LC Distribution Module, OptiSPEED, UHD Panel

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Brand	SYSTIMAX 360™ iPatch®

General Specifications

Color	Black
Intelligence Type	iPatch® enabled
Interface, front	LC
Rack Units	2
Shelf Movement	Fixed
Total Ports, quantity	144

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	492.76 mm 19.4 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)
----------------------	--

Optical Specifications

760188433 | 360G2-iP-2U-288F-LC-DM-OS-UHD

Fiber Mode Multimode

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard Austel | CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

