



SYSTIMAX 360™ PATCHMAX® Panel Kit, 2U, 24 port

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	RJ45 patch panel
Product Brand	GigaSPEED X10D®

General Specifications

Cable Type	Unshielded
Color	Cool gray Satin chrome
Intelligence Type	iPatch® ready
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	2
Total Ports, quantity	24

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth, with cable management	266.7 mm 10.5 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing

760108993 | 360-PM-KIT-2U-24

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

