



## SYSTIMAX 360™ GigaSPEED X10D® and GigaSPEED XL® Evolve Angled 2U U/UTP Panel Kit

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	RJ45 patch panel
<b>Product Brand</b>	GigaSPEED X10D®   SYSTIMAX 360™

### General Specifications

<b>Cable Type</b>	Unshielded
<b>Color</b>	Cool gray   Satin chrome
<b>Intelligence Type</b>	iPatch® ready
<b>Panel Style</b>	Angled
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	2
<b>Total Ports, quantity</b>	48
<b>Wiring</b>	T568A   T568B

### Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	482.6 mm   19 in
<b>Depth, with cable management</b>	266.7 mm   10.5 in

### Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Powder-coated steel
----------------------	---

### Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

# 760152793 | 360-A-E-KIT-2U

---

<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	1.497 kg   3.3 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

