

760224071 | 360DMis-12LC-LS



G2 LL Multimode OM4 MPO 12 distribution module, 12 LC to 1x12f MPO pinned, internal shutters

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	InstaPATCH® 360
Product Series	G2

General Specifications

Functionality	Breakout
Color, front	Aqua
Color, rear	Gray
Intelligence Type	Not iPatch® ready
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up/up Pinned
Polarity	Method B
Shuttered	Yes
Total Fibers, quantity	12

Dimensions

Height	25.51 mm 1.004 in
Width	95.91 mm 3.776 in
Depth	119.69 mm 4.712 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4
Insertion Loss, maximum	0.47 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.095 kg | 0.209 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant

