

760224113 | 360DMis-12LC-WB



G2 LL Multimode OM5 MPO 12 distribution module, 12 LC to 1x12f MPO pinned, internal shutters

- LazrSPEED® WideBand extends the capability of OM4 across enough spectrum to support at least four low-cost wavelengths

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	InstaPATCH® 360
Product Series	G2

General Specifications

Functionality	Breakout
Color, front	Lime green
Color, rear	Gray
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up/up Pinned
Polarity	Method B
Shuttered	Yes
Total Fibers, quantity	12

Dimensions

Height	25.51 mm 1.004 in
Width	95.91 mm 3.776 in
Depth	119.69 mm 4.712 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM5
Insertion Loss, maximum	0.47 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.095 kg | 0.209 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant

