



Shielded Discrete Distribution Module, SL, (4 ea/pkg), Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Module

General Specifications

Color	Black
--------------	-------

Dimensions

Height	41.148 mm 1.62 in
Width	106.68 mm 4.2 in
Depth	32.512 mm 1.28 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity	4
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

760238661 | CPP-SDDM-SL-KIT-4PK

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

