

760238950 | FD-8-2U-A



2RU patch panel which interfaces with QSFP ports to easily break them out in LC connections. The MPO and LC ports are both front facing for easy mapping and patching. 20 singlemode MPO-8 pinned and 80 duplex shuttered LC ports, Method A

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FD

General Specifications

Color	Black
Interface, front	LC/UPC MPO
Interface Feature, front	Pinned
Rack Units	2
Shelf Movement	Fixed
Total Ports, quantity	180

Dimensions

Height	82.55 mm 3.25 in
Width	482.6 mm 19 in
Depth	292.1 mm 11.5 in

Optical Specifications

Insertion Loss, maximum	0.6 dB
--------------------------------	--------

Environmental Specifications

Safety Standard	UL 60950
------------------------	----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

