

# FD3-AE144J00GBBP4

---



FDH 3000 Small Fiber Distribution Cabinet, 144F, SC/APC, no splitters, single armor loose tube, 100 ft, 48F

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution hub
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Access</b>	Front
<b>Cable Type</b>	Armored - Single Loose Tube
<b>Color</b>	Putty white
<b>Distribution Cables, quantity</b>	1
<b>Distribution Ports, quantity</b>	288
<b>Fibers per Distribution Cable, quantity</b>	144
<b>Fibers per Feeder Cable, quantity</b>	48
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pad
<b>Splitter Slots, quantity</b>	12

## Dimensions

<b>Height</b>	914 mm   35.984 in
<b>Width</b>	686 mm   27.008 in
<b>Depth</b>	457 mm   17.992 in
<b>Cable Length</b>	30.48 m   100 ft
<b>Enclosure Size</b>	Small

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Aluminum

# FD3-AE144J00GBBP4

---

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

