FD3-AE144J00JBBP2



FDH 3000 Small Fiber Distribution Cabinet, 144F, SC/APC, no splitters, dielectric loose tube, 100 ft, 24F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeDielectric - Loose Tube

Color Putty white

Distribution Cables, quantity 1

Distribution Ports, quantity 144

Fibers per Distribution Cable, quantity 144

Fibers per Feeder Cable, quantity 24

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Splitter Slots, quantity 12

Dimensions

 Height
 914 mm
 | 35.984 in

 Width
 686 mm
 | 27.008 in

 Depth
 457 mm
 | 17.992 in

 Cable Length
 30.48 m
 | 100 ft

Enclosure Size Small

Material Specifications

Finish Powder coated

Material Type Aluminum

COMMSCOPE®

FD3-AE144J00JBBP2

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

