FD3-AE144J2AJBBP1



FDH 3000 Small Fiber Distribution Cabinet, 144F, SC/APC,(2) 32-splitter modules, dielectric loose tube, 100 ft, 12F

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000
General Specifications	
Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	288
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Split Ratio	Symmetrical
Splitter Slots, quantity	12
Splitter Type	1 x 32
Splitter, quantity	2
Dimensions	
Height	914 mm 35.984 in
Width	686 mm 27.008 in
Depth	457 mm 17.992 in
Cable Length	30.48 m 100 ft
Enclosure Size	Small

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 18, 2024



FD3-AE144J2AJBBP1

Material Specifications

FinishPowder coatedMaterial TypeAluminumEnvironmental SpeceAbove groundPackaging and Weights1Packaging quantity1Packaging TypePalletRegulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSAbove maximum concentration valueREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliant/ExemptedUK-ROHSCompliant/Exempted



Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 18, 2024

