# FD3-AE288J00GGBP2



FDH 3000 Small Fiber Distribution Cabinet, 288F, SC/APC, no splitters, single armor loose tube, 100 ft, 24F

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution hub

**Product Series** FDH 3000

### General Specifications

**Access** Front

Cable TypeArmored - Single Loose Tube

**Color** Putty white

Distribution Ports, quantity 288
Fibers per Feeder Cable, quantity 24

Interface, Input SC

Interface Feature, Input APC

**Mounting** Pad

Splitter Slots, quantity 12

#### **Dimensions**

 Height
 914.4 mm | 36 in

 Width
 685.8 mm | 27 in

 Depth
 457.2 mm | 18 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Small

## Material Specifications

**Finish** Powder coated

Material Type Aluminum



# FD3-AE288J00GGBP2

## **Environmental Specifications**

**Environmental Space** Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

