

# FD3-AG360J00GDBP2

---



FDH 3000 Fiber Distribution Medium Cabinet, 360F, SC/APC, no splitters, single armor loose tube, 100 ft, 24F

## Product Classification

|                              |                        |
|------------------------------|------------------------|
| <b>Regional Availability</b> | North America          |
| <b>Product Type</b>          | Fiber distribution hub |
| <b>Product Series</b>        | FDH 3000               |

## General Specifications

|  |                             |
|--|-----------------------------|
| <b>Access</b>                            | Front                       |
| <b>Cable Type</b>                        | Armored - Single Loose Tube |
| <b>Color</b>                             | Putty white                 |
| <b>Distribution Cables, quantity</b>     | 3                           |
| <b>Distribution Ports, quantity</b>      | 432                         |
| <b>Fibers per Feeder Cable, quantity</b> | 24                          |
| <b>Interface, Input</b>                  | SC                          |
| <b>Interface Feature, Input</b>          | APC                         |
| <b>Mounting</b>                          | Pad                         |
| <b>Splitter Slots, quantity</b>          | 24                          |

## Dimensions

|                       |                    |
|-----------------------|--------------------|
| <b>Height</b>         | 1,066.8 mm   42 in |
| <b>Width</b>          | 685.8 mm   27 in   |
| <b>Depth</b>          | 457.2 mm   18 in   |
| <b>Cable Length</b>   | 30.48 m   100 ft   |
| <b>Enclosure Size</b> | Medium             |

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Aluminum      |

# FD3-AG360J00GDBP2

---

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

