FD3-AG432J2ALCBP4



FDH 3000 Fiber Distribution Medium Cabinet, 432F, SC/APC, (2) 32-splitter modules, armored ribbon, 100 ft, 48F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeArmored - Ribbon

Color Putty white

Distribution Cables, quantity 2

Distribution Ports, quantity 432

Fibers per Distribution Cable, quantity 216

Fibers per Feeder Cable, quantity 48

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Split Ratio Symmetrical

Splitter Slots, quantity 24

Splitter Type 1 x 32

Splitter, quantity 2

Dimensions

 Height
 1,066.8 mm | 42 in

 Width
 686 mm | 27.008 in

 Depth
 457 mm | 17.992 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Medium



FD3-AG432J2ALCBP4

Material Specifications

Finish Powder coated

Material Type Aluminum

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

