## FD3-AJ576J1AJBBP7



FDH 3000 Fiber Distribution Large Cabinet, 576F, SC/APC, 32-splitter module, dielectric loose tube, 100 ft, 72F

### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution hub

Product Series FDH 3000

General Specifications

**Access** Front and rear door

Cable TypeDielectric - Loose Tube

**Color** Putty white

**Distribution Cables, quantity** 4

**Distribution Ports, quantity** 576

Fibers per Distribution Cable, quantity 144

Fibers per Feeder Cable, quantity 72

Interface, Input SC

Interface Feature, Input APC

**Mounting** Pad

**Split Ratio** Symmetrical

Splitter Type 1 x 32

Splitter, quantity 1

#### Dimensions

**Height** 1,238.25 mm | 48.75 in

**Width** 1,220.47 mm | 48.05 in

**Depth** 497.33 mm | 19.58 in

**Cable Length** 30.48 m | 100 ft

Enclosure Size Large

Material Specifications

COMMSC PE®

# FD3-AJ576J1AJBBP7

**Finish** Powder coated

Material Type Aluminum

**Environmental Specifications** 

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

