# FD3-AJ648J2AGCBP4

FDH 3000 Fiber Distribution Large Cabinet, 648F, SC/APC,(2) 32-splitter modules, single armor loose tube, 100 ft, 48F

## Product Classification

| | |
|---|---|
| **Regional Availability** | North America |
| **Product Type** | Fiber distribution hub |
| **Product Series** | FDH 3000 |

## General Specifications

| | |
|---|---|
| **Access** | Front and rear door |
| **Cable Type** | Armored - Single Loose Tube |
| **Color** | Putty white |
| **Distribution Cables, quantity** | 3 |
| **Distribution Ports, quantity** | 648 |
| **Fibers per Distribution Cable, quantity** | 216 |
| **Fibers per Feeder Cable, quantity** | 48 |
| **Interface, Input** | SC |
| **Interface Feature, Input** | APC |
| **Mounting** | Pad |

## Dimensions

| | |
|---|---|
| **Height** | 1,238.25 mm  \|  48.75 in |
| **Width** | 1,220.47 mm  \|  48.05 in |
| **Depth** | 497.33 mm  \|  19.58 in |
| **Cable Length** | 30.48 m  \|  100 ft |
| **Enclosure Size** | Large |

## Material Specifications

| | |
|---|---|
| **Finish** | Powder coated |
| **Material Type** | Aluminum |

COMMSCOPE®

# FD3-AJ648J2AGCBP4

## Environmental Specifications

**Environmental Space**                              Above ground

## Packaging and Weights

**Packaging quantity**                               1

**Packaging Type**                                   Pallet

## Regulatory Compliance/Certifications

| Agency | Classification |
|---|---|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

COMMSCOPE®