FD3-AJ864J00GABP4



FDH 3000 Fiber Distribution Large Cabinet, 864F, SC/APC, no splitters, single armor loose tube, 100 ft, 48F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front and rear door

 Cable Type
 Armored - Single Loose Tube

Color Putty white

Distribution Cables, quantity 12

Distribution Ports, quantity 864

Fibers per Distribution Cable, quantity 72

Fibers per Feeder Cable, quantity 48

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Splitter Slots, quantity 48

Dimensions

Height 1,238.25 mm | 48.75 in

Width 1,220.47 mm | 48.05 in

Depth 497.33 mm | 19.58 in

Cable Length 30.48 m | 100 ft

Enclosure Size Large

Material Specifications

Finish Powder coated

Material Type Aluminum

COMMSC PE°

FD3-AJ864J00GABP4

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

