FD3-AJ864J00JCBP7



FDH 3000 Fiber Distribution Large Cabinet, 864F, SC/APC, no splitters, dielectric loose tube, 100 ft, 72F

Product Classification

| Regional Availability | North America | |
|---|-----------------------------|--|
| Product Type | Fiber distribution hub | |
| Product Series | FDH 3000 | |
| General Specifications | | |
| Access | Front and rear door | |
| Cable Type | Dry Dielectric - Loose Tube | |
| Color | Putty white | |
| Distribution Cables, quantity | 4 | |
| Distribution Ports, quantity | 864 | |
| Fibers per Distribution Cable, quantity | 216 | |
| Fibers per Feeder Cable, quantity | 72 | |
| Interface, Input | SC | |
| Interface Feature, Input | APC | |
| Mounting | Pad | |
| Splitter Slots, quantity | 48 | |
| Dimensions | | |
| Height | 1,238.25 mm 48.75 in | |
| Width | 1,220.47 mm 48.05 in | |
| Depth | 497.33 mm 19.58 in | |
| Cable Length | 30.48 m 100 ft | |
| Enclosure Size | Large | |
| Material Specifications | | |
| Finish | Powder coated | |
| Material Type | Aluminum | |

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 14, 2024



FD3-AJ864J00JCBP7

Environmental Specifications

Environmental Space

Above ground

Packaging and Weights

Packaging quantity

Packaging Type

Agency

Pallet

1

Regulatory Compliance/Certifications

Classification

| REACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliant/Exempted | CHINA-ROHS | Above maximum concentration value |
|---|------------|---|
| ROHS Compliant/Exempted | REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| | ROHS | Compliant/Exempted |
| UK-ROHS Compliant/Exempted | UK-ROHS | Compliant/Exempted |



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 14, 2024

