FD3-PA036J00M2210



FDH 3000 Fiber Distribution Hub in a Pedestal, 36F, SC/APC, no splitters, ribbon pigtails, 48 splice cap., 6F spliced feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

Product Classification

Regional Availability North America

Product Type Hub in a pedestal

Product Series FDH 3000

General Specifications

Access Front

Cable TypePigtails - Ribbon

Color Putty white

Distribution Ports, quantity 36

Fibers per Feeder Cable, quantity 6

Interface, Input SC

Interface Feature, Input APC

Mounting Pedestal

Splice Tray Included, quantity 2

Splice Tray Type Included 24-way, heat shrink

Splicing Capacity, maximum 36
Splitter Slots, quantity 6

Dimensions

Enclosure Size Small

Material Specifications

Finish Powder coated



FD3-PA036J00M2210

Material Type Molded plastic

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Included Cable clamps (2)

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

