

# FD3-PA072J00M3210

---



FDH 3000 Fiber Distribution Hub in a Pedestal, 72F, SC/APC, no splitters, ribbon pigtails, 72 splice cap., 6F spliced feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Hub in a pedestal
<b>Product Series</b>	FDH 3000

## General Specifications

<b>Access</b>	Front
<b>Cable Type</b>	Pigtails - Ribbon
<b>Color</b>	Putty white
<b>Distribution Ports, quantity</b>	72
<b>Fibers per Feeder Cable, quantity</b>	6
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Pedestal
<b>Splice Tray Included, quantity</b>	3
<b>Splice Tray Type Included</b>	24-way, heat shrink
<b>Splicing Capacity, maximum</b>	72
<b>Splitter Slots, quantity</b>	6

## Dimensions

<b>Enclosure Size</b>	Small
-----------------------	-------

## Material Specifications

<b>Finish</b>	Powder coated
---------------	---------------

# FD3-PA072J00M3210

---

**Material Type** Molded plastic

## Environmental Specifications

**Environmental Space** Above ground

## Packaging and Weights

**Included** Cable clamps (2)

**Packaging quantity** 1

**Packaging Type** Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

